



Pass and Seymour  
**Turnlok® 67W49 Watertight Single Receptacle, Yellow**  
Part No. 67W49



Turnlok Watertight Single Receptacle, 20amp 277volt, NEMA Configuration L7-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033625	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Phase	Single	Number of Wires	3
-------	--------	-----------------	---

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	<p>Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug &amp; Connector only)</p> <p>Flammability UL94V0 (boxes &amp; wiring device interiors)</p> <p>Operating Temperature -40°C (without impact) to +60°C</p> <p>continuous UV resistance All exposed materials are UV stabilized</p>