



Single-Pole, Double Combination Switch, 15A, 120/277V, With Ground, Ivory.

## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007690132
Country Of Origin	Mexico	Features	Combination
Number of Switches	2	Application Sector	Commercial, Residential
Standard	UL 498	Type	Combination

### Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Connection	Side Wire	Contact Rating	15Amp, 120/277Vac
------------	-----------	----------------	-------------------

---

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

---

Wire Size	#14 - #10 AWG	Voltage	120.0 V
-----------	---------------	---------	---------

---