



**Pass and Seymour**  
**15A 120V/125V Combination Single-Pole Toggle Switch and Tamper-Resistant Single Receptacle, Brown**  
Part No. 691TR



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Easily accessible break-off separate or common feed.

One-piece heat-treated triple-wipe brass power contacts.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007242454
Country Of Origin	Mexico	Features	Combination
Number of Switches	1	Application Sector	Commercial, Residential
Standard	UL20, UL498	Type	Combination

### Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

---

Is Tamper-Resistant	Yes	Contact Configuration	N-0
Operating Cycles	30000	Connection	Side Wire
Contact Rating	15 Amp, 120/125 VAC	Amperage	15 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Environmental Conditions	Flammability: UL94 V2		

---