

Turnlok® Receptacle 3-Pole 3-Wire 20A 125/250V



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007731002
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498, FEDSPEC		

### Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Height US	2.25 in		

### Technical Information

---

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	125.0 V

---