



8 outlet plug-in workstation surge protector

Features & Benefits

8 outlets spaced for plugin transformers	Lighted switch
Impact-resistant putty white polymeric housing	15A
6' (1.8m) 14/3 SJT putty white cord with NEMA 5-15 plug	Maximum surge

Specifications

General Info

Product Line	Wiremold	UPC Number	024006000017
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	14.0 in	Product Weight US	2.3 lb
Product Height US	1.5 in	Product Length US	4.25 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Connection	Cord-ended
-------	--------------	------------	------------

Class	75	Amperage	15 A
-------	----	----------	------

Short Circuit Rating	6500 Amps	Response Time	<1 ns
----------------------	-----------	---------------	-------

Mounting Type	Keyhole	Mounting	Yes
---------------	---------	----------	-----

Type of Indicators	LED	Voltage	120.0 V
--------------------	-----	---------	---------

Environmental Conditions	Indoor, dry location
--------------------------	----------------------
