



## Pass and Seymour Double Pole, Single Phase AC Manual Motor Controller Part No. 7832MD



Double Pole, Single Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

### Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Matte	UPC Number	785007267679
Country Of Origin	United States	Standard	CSA Listed, UL Listed

#### Dimensions

Product Width US	4.5 in	Product Depth US	1.8 in
Product Height US	5.75 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Operating Cycles	50000	Connection	Side & Back Wired
Amperage	30 A	Number of Poles	Double Pole
Wire Size	#14 - #10 AWG	Environmental Conditions	UL94 V2

---