



Three pole, Three Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.

Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Matte	UPC Number	785007267709
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed
Type	Manual Controller		

Dimensions

Product Width US	4.5 in	Product Depth US	1.8 in
Product Height US	5.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50000	Connection	Side & Back Wired
------------------	-------	------------	-------------------

Amperage	30 A	Enclosure Type	NEMA 3R
----------	------	----------------	---------

Wire Size	#14 - #10 AWG	Voltage	600.0 V
-----------	---------------	---------	---------

Environmental Conditions	UL94 V2
--------------------------	---------
