



Manual Control Switch 2-Pole 60A 600V in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

- High horsepower rating, up to 3HP for heavy-duty applications
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).
- Compact design provides ease of installation
- Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life
- Made in USA
- Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements
- Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom
- Accepts #4 AWG
- cULus listed

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007078619
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed	Type	Manual Controller

Dimensions

Product Width US	1.74 in	Product Depth US	1.66 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Horsepower Rating	3 HP @ 120 VAC	Connection	Hardwired
-------------------	----------------	------------	-----------

Amperage	60 A	Enclosure Type	NEMA 3R
----------	------	----------------	---------

Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

Maximum Horsepower Rating	3 HP @ 120 VAC	Wiring Location	Bottom
---------------------------	----------------	-----------------	--------

Voltage	600.0 V		
---------	---------	--	--
