




Wiremold
8801S-FC Omnibox Series Fire Classified 1-Gang Floor Box
Part No. 8801S-FC



1-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum. Use in normal weight concrete 4 1/2" (114mm) minimum pour over deck. One 1 1/4" (32mm) conduit feed opening. Box Capacity 53 cubic inches. This floor box preserves the 2-hour fire rating of floors in which it has been installed.

Features & Benefits

1-Gang Fire Classified Steel Floor Box.

Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum.

Use in normal weight concrete 4 1/2" (114mm) minimum pour over deck. One 1 1/4" (32mm) conduit feed opening. Box Capacity 53 cubic inches.

This floor box preserves the 2-hour fire rating of floors in which it has been installed.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|--|
| Product Line | Wiremold | UPC Number | 786776183146 |
| Country Of Origin | United States | Construction | Assembled |
| Cover Style | Flush | Application Sector | Commercial |
| Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Floor Box | | |

Dimensions

| | | | |
|-------------------|---------|----------------|--------------------|
| Product Weight US | 24.0 lb | Cubic Capacity | 53 in ³ |
| Knockout Size | 1 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Additional Information

RoHS Compliant Yes

Technical Information

Floor Type Concrete Service Capacity Single

Minimum Floor Depth 2 in Fire Rating 2 hr

Box Capacity 1 Gang Cable Entry conduit Feed Channels

Box Type Fire Classified Number of Outlets 2

Depth Behind Device Plates 2.75 in
