




Wiremold
8801S-FC2 Omnibox Series Fire Classified 1-Gang Floor Box
Part No. 8801S-FC2



1-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 6-1/2" (165mm) maximum. One 2" (51mm) conduit feed opening. Box Capacity - 53 cubic inches. This box preserves up to a 3-hour fire rating of floors in which it has been installed.

Features & Benefits

1-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 6-1/2" (165mm) maximum. One 2" (51mm) conduit feed opening. Box Capacity - 53 cubic inches.

This box preserves up to a 3-hour fire rating of floors in which it has been installed

Specifications

General Info

Product Line	Wiremold	UPC Number	786776184181
Country Of Origin	United States	Construction	Assembled
Cover Style	Flush	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	11.375 in	Product Weight US	20.0 lb
Product Depth US	3.5 in	Product Length US	14.5 in
Cubic Capacity	53 in ³	Knockout Size	1 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Concrete	Service Capacity	Single
------------	----------	------------------	--------

Minimum Floor Depth	2 in	Fire Rating	3 hr
---------------------	------	-------------	------

Box Capacity	1 Gang	Cable Entry	CONDUIT
--------------	--------	-------------	---------

Box Type	Fire Classified	Depth Behind Device Plates	2.75 in
----------	-----------------	----------------------------	---------
