




**Wiremold**  
**8802S-FC Omnibox Series Fire Classified 2-Gang Floor Box**  
Part No. 8802S-FC



2-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum. Two 1 1/4" (32mm) conduit feed openings. Box Capacity - 58.5 cubic inches per gang. This floor box preserves the 2-hour fire rating of floors in which it has been installed.

## Features & Benefits

2-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum. Two 1 1/4" (32mm) conduit feed openings. Box Capacity - 58.5 cubic inches per gang.

This floor box preserves the 2-hour fire rating of floors in which it has been installed.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776183153
Country Of Origin	United States	Construction	Assembled
Cover Style	Flush	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

### Dimensions

Product Weight US	28.0 lb	Cubic Capacity	117 in <sup>3</sup>
Knockout Size	1 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

## Additional Information

---

RoHS Compliant      Yes

---

## Technical Information

---

Floor Type      Concrete      Service Capacity      Dual

---

Minimum Floor Depth      2 in      Fire Rating      3 hr

---

Box Capacity      2 Gangs      Cable Entry      conduit Feed Channels

---

Box Type      Fire Classified      Number of Outlets      4

---

Depth Behind Device Plates      2.75 in

---