




**Wiremold**  
**8803S-FC Omnibox Series Fire Classified 3-Gang Floor Box**  
Part No. 8803S-FC



3-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum. Three 1 1/4" (32mm) conduit feed openings. Inside Gang Capacity - 67.5 cubic inches. Outside Gang Capacity - 54 cubic inches each gang. This floor box preserves the 2-hour fire rating of floors in which it has been installed.

## Features & Benefits

3-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 5" (127mm) maximum.

Three 1 1/4" (32mm) conduit feed openings. Inside Gang Capacity - 67.5 cubic inches. Outside Gang Capacity - 54 cubic inches each gang. This floor box preserves the 2-hour fire rating of floors in which it has been installed.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776183160
Country Of Origin	United States	Construction	Assembled
Cover Style	Flush	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

### Dimensions

Product Weight US	35.0 lb	Cubic Capacity	175.5 in <sup>3</sup>
Knockout Size	1 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Floor Type	Concrete	Service Capacity	Triple
Minimum Floor Depth	2 in	Fire Rating	2 hr
Box Capacity	3 Gangs	Cable Entry	conduit Feed Channels
Box Type	Fire Classified	Number of Outlets	6
Depth Behind Device Plates	2.75 in		

---