




**Wiremold**  
**8803S-FC12 Omnibox Series Fire Classified 3-Gang Floor Box**  
Part No. 8803S-FC12



3-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 6-1/2" (165mm) maximum. One 1 1/4" (32mm) and two 2" (51mm) conduit feed openings. Inside Gang Capacity - 67.5 cubic inches. Outside Gang Capacity - 54 cubic inches each gang. This floor box preserves up to a 3- hour fire rating of floors in which it has been installed.

## Features & Benefits

3-Gang Fire Classified Steel Floor Box. Adjustment range over deck of 2" (51mm) minimum to 6-1/2" (165mm) maximum.

This floor box preserves up to a 3- hour fire rating of floors in which it has been installed.

One 1 1/4" (32mm) and two 2" (51mm) conduit feed openings. Inside Gang Capacity - 67.5 cubic inches. Outside Gang Capacity - 54 cubic inches each gang.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776184204
Country Of Origin	United States	Construction	Assembled
Cover Style	Flush	Number of Knockouts	1
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

### Dimensions

Product Width US	11.375 in	Product Weight US	30.0 lb
Product Depth US	3.5 in	Product Length US	20.0 in
Cubic Capacity	54 in <sup>3</sup>	Knockout Size	1 in

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Floor Type	Concrete	Service Capacity	Triple
------------	----------	------------------	--------

---

Minimum Floor Depth	2 in	Fire Rating	3 hr
---------------------	------	-------------	------

---

Box Capacity	3 Gangs	Cable Entry	CONDUIT
--------------	---------	-------------	---------

---

Box Type	Fire Classified	Depth Behind Device Plates	2.75 in
----------	-----------------	----------------------------	---------

---