



Pass and Seymour
Trademaster® 15A 125V Tamper-Resistant 8-Hole/Push Wire Duplex Receptacle, White
Part No. 880TRW



Our Pass and Seymour TradeMaster receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code (NEC). For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Meets 2008 National Electrical Code Tamper-Resistant requirements. High-impact resistant thermoplastic construction.

Extra-long strap.

Quickloop wire looping aid.

Long-term blade retention.

Extra-large circuit break-off tabs.

Side-access push wire release.

Ultrasonic welding of face to back body.

Traditional contoured face (3232 models).

Self-grounding models provide automatic ground clip.

Specifications

General Info

| | | | |
|-------------------|-------------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007008371 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial, Residential |
| Standard | UL498, CSA C22.2 No. 42 | Type | Outlet |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|---------------------|-----|--------------------|--------------|
| Is Tamper-Resistant | Yes | Temperature Rating | -30° - 60° C |
|---------------------|-----|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|--------|----------------|--------|
| Wire Size | 14 AWG | Indoor/Outdoor | Indoor |
|-----------|--------|----------------|--------|
