

Dual 3-Speed Fan Control with 1.5A 300W Dimmer



Features & Benefits

Fits one gang box.

Controls both fan speed and light level.

Decorator styling.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007943184
Country Of Origin	Mexico	Product Series	Trademaster
Features	Combination, Fan Control	Switch Type	Rotary, Single Pole
Number of Switches	2	Application Sector	Residential
Standard	RoHS, CSA Listed, UL Listed	Warranty Type	Limited Lifetime Warranty

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

Technical Information

Load Rating	120V 1.5A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)	Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Speed Range	Variable
Voltage	120 VAC	Load Type	Fan Motor, Incandescent
Environmental Conditions	Indoor Only		
