



Cablofil  
**CabloPort Block 10" Long [943524]**  
 Part No. 943524



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

## Features & Benefits

Cable pathway or other products mounted to base with clamps and screws.

Install: on any roofing material or other flat surface.

Curb style: maximum load 500 lbs. (CP5 - maximum load 150 lbs.).

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Composite material: allows through bolts or lag type screws (through bolts recommended)

## Specifications

### General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019096	Country Of Origin	Canada
Standard	UL Classified		

### Dimensions

Product Width US	6.0 in	Product Weight US	4.6 lb
Product Volume US	0.133 cu ft	Product Depth US	9.6 in
Product Height US	4.0 in		

---

## Trade Programs

---

BAA	Yes
-----	-----

---