



Ortronics  
**Discontinued - Avaya AA1403011-BXU Compatible 10GBase-BX SFP+ Transceiver (SMF, Tx: 1270nm Rx: 1330nm, 10-20km, LC Duplex, DDM, I-Temp)**  
Part No. AA1403011-BXU-L

Avaya AA1403011-BXU Compatible 10GBase-BX SFP+ Transceiver (SMF, Tx: 1270nm Rx: 1330nm, 10-20km, LC Duplex, DDM, I-Temp)



## Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

|                   |             |               |              |
|-------------------|-------------|---------------|--------------|
| Product Line      | Ortronics   | UPC Number    | 662875078531 |
| Country Of Origin | China       | Warranty Type | Lifetime     |
| Type              | Transceiver |               |              |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 13.7 mm | Product Depth US | 56.6 mm |
| Product Height US | 12.8 mm |                  |         |

### Technical Information

|                           |             |                           |           |
|---------------------------|-------------|---------------------------|-----------|
| Fiber Optic Cable Type    | Single-Mode | Max Distance Support      | 20 km     |
| Operating Temperature Min | -40 °C      | Operating Temperature Max | 85 °C     |
| Data Transfer Rate        | 10 Gbps     | Connector Type            | LC Duplex |
| Form Factor               | SFP+        |                           |           |