



Upgrade your fan's speed control and stop using those clunky, hard-to-reach fan cords. Now you can adjust the speed of your ceiling fan quietly, and in style, thanks to the adorne Collection.



This fan speed control switch features four speed settings and a sleek on/off switch. Use on its own to control a fan from one location, or pair with a 3-way switch and conveniently control a single fan from two locations.

This switch\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features easy on/off control, as well as four speed settings.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007023305
Country Of Origin	China	Features	Antimicrobial Protection, Fan Control

---

Switch Type	Paddle	Number of Switches	1
-------------	--------	--------------------	---

---

Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
------------------------	-----------	----------------------	-----------

---

Application Sector	Residential	Standard	cULus
--------------------	-------------	----------	-------

---

Warranty Type	Limited Lifetime Warranty
---------------	---------------------------

---

## Dimensions

---

Product Width US	1.85 in	Product Depth US	1.77 in
------------------	---------	------------------	---------

---

Product Height US	2.66 in
-------------------	---------

---

## Technical Information

---

Connection	Screw Terminals	Number of Gangs	1
------------	-----------------	-----------------	---

---

Amperage	1.6 A	Number of Poles	3-Way, Single Pole
----------	-------	-----------------	--------------------

---

Wire Size	#14 - #10 AWG	Wattage	700 W
-----------	---------------	---------	-------

---

Mounting Type	Box	Speed Range	4-Speed
---------------	-----	-------------	---------

---

Connection Type	Internal Pressure Plates
-----------------	--------------------------

---