



Wiremold
AC Series™ AC10105 Eight Gang Raised Floor Box with Gray Carpet style Lid
Part No. AC10105-2



With a 5 inch (127mm) depth, the AC Series™ AC10105 Raised Floor Box provides eight gangs of power and/or communication device capacity. Power plate with duplex knockouts included with box. It also provides increased plug-in volume which is ideal for the additional space needed when plugging in transformer type plugs. Lids can be rotated 180° for easy orientation. Gray lids are die-cast zinc construction, and allow for a carpet or tile insert.

Features & Benefits

This product meets the material restrictions of RoHS

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564018773	Country Of Origin	United States
Construction	Assembled	Number of Knockouts	2
Cover Material	Die-Cast Zinc	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	11.5 in	Product Weight US	17.05 lb
Product Volume US	677.78 cu in	Product Depth US	11.5 in
Product Height US	5.13 in	Cubic Capacity	115 in ³

Knockout Size	1/2 in, 3/4 in
---------------	----------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Raised	Service Capacity	Triple
------------	--------	------------------	--------

Minimum Floor Depth	5 in	Box Capacity	8 Gangs
---------------------	------	--------------	---------

Cable Entry	knockout	Box Type	Recessed
-------------	----------	----------	----------

Number of Outlets	0	Depth Behind Device Plates	2 in
-------------------	---	----------------------------	------
