



On-Q Compression RG6U-Quad F Plug Part No. AC300810



Ensure reliable and secure connections with the Compression RG6U-Quad F Plug. This water-resistant F compression connector is designed for RG6/U Quad Shield Coax, making it a preferred choice for many satellite and cable TV service providers. It features a robust design that passes a 55 lbs pull test and meets IPS-TP13 moisture resistance standards, ensuring durability and long-lasting performance. The connector allows for quick and efficient termination with a simple squeeze of the handle. Available in a convenient pack of 10.

Features & Benefits

Seat and cut all wires at once with a squeeze of the handle

Pull Test: 55 lbs

Moisture Resistant: IPS-TP13

Available in 10 and 50 packs

Specifications

General Info

Product Line	On-Q	UPC Number	804428121831
Country Of Origin	Taiwan, Province Of China	Application Sector	Residential
Standard	RoHS		

Technical Information

Conductor Range	0.022 to 0.042 (diameter)	Connection	Shell and nut are nickel-plated brass
Temperature Rating	167° F	Amperage	10 A
Environmental Conditions	0		