



On-Q
Cat 6 Patch Cable, 7 ft, Blue
Part No. AC3607BEV1



This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested and exceed the patch cable standard.

Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.

Specifications

General Info

Product Line	On-Q	Color	Blue
UPC Number	804428066835	Country Of Origin	China

Dimensions

Product Length US	7.0 FT
-------------------	--------

Technical Information

Jacket Material	PVC	Wire Gauge	24 AWG
Cable Type	Cat6	Cable Diameter	0.25 in