



This box has a 4" (102mm) depth design with an extra 2" (51mm) of width for additional wiring capacity. These boxes can accommodate two duplex power receptacles on one side. Power plate with duplex knockouts included with box. The communication plate will accept two communication adapters for up to 12 ports of activation. Lids can be rotated 180° for easy orientation. Gray lids are die-cast zinc construction. NOTE: For custom options, consult factory. All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs. All communication plates sold separately.

Features & Benefits

This box has a 4" (102mm) depth design with an extra 2" (51mm) of width for additional wiring capacity. These boxes can accommodate two duplex power receptacles on one side.

Power plate with duplex knockouts included with box. The communication plate will accept two communication adapters for up to 12 ports of activation. Lids can be rotated 180° for easy orientation. Gray lids are die-cast zinc construction.

All communication plates sold separately.

NOTE: For custom options, consult factory. All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564521167
Country Of Origin	United States	Construction	Assembled
Cover Material	Die-Cast Zinc	Application Sector	Commercial
Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	10.0 in	Product Weight US	11.3 lb
------------------	---------	-------------------	---------

Product Depth US	4.0 in	Product Length US	8.0 in
------------------	--------	-------------------	--------

Knockout Size	1/2 in, 3/4 in
---------------	----------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Raised	Service Capacity	Dual
------------	--------	------------------	------

Minimum Floor Depth	4 in	Box Capacity	4 Gangs
---------------------	------	--------------	---------

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

Depth Behind Device Plates	1.63 in
----------------------------	---------
