



Perfect for garages and pantries, this dimmer switch allows for both manual and automatic motion-activated control. Using motion-sensing technology, it automatically turns lights on when you enter a room, and off when you leave. With manual control, you can even adjust to your preferred light level with the subtle built-in slider. Use on its own to control an incandescent or halogen light or fixture from a single location, or pair with a second Motion Sensor Dimmer to use as a remote dimmer switch for control of a single light source from two locations. This Motion Sensor Dimmer is meant for single fixtures and small lighting groups that do not exceed 700W.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adore® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with dimmable incandescent/halogen bulbs or fixtures. Features manual control (for power and light level), as well as automatic control through motion-sensing technology.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-----------------------|-----------------------|------------------------|---|
| Product Line | Pass & Seymour | Color | White |
| Finish | Gloss | UPC Number | 785007023428 |
| Country Of Origin | China | Features | Adjustable Time Delay, Antimicrobial Protection, Dimming, Light Level Sensor, Motion Sensor |
| Switch Type | Motion Sensor, sofTap | Number of Switches | 1 |
| Installation Location | Wall Box | Device Front Face Size | Full-Size |

| | | | |
|------------------------------|---|-------------------------|---|
| Device Backbody Size | Plus-Size | Application Sector | Hospitality, Light Commercial, Multi-Dwelling Unit, Residential |
| Standard | cULus | Warranty Type | Limited Lifetime Warranty |
| Dimensions | | | |
| Product Width US | 1.85 in | Product Depth US | 1.77 in |
| Product Height US | 4.2 in | | |
| Technical Information | | | |
| Load Rating | 120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent) | Sensor Coverage Pattern | 180 deg |
| Sensor Type | Occupancy, Vacancy | Timer Duration | 15 Minutes, 30 Seconds-30 Minutes |
| Number of Poles | Single Pole 3 Way | Wire Size | #14 - #10 AWG |
| Trim/Adjustment Level | Button | Dimming Phase | Forward |
| Input Voltage | 120 VAC | Requires Neutral Wire | No |
| Line Frequency | 60 Hz | Indoor/Outdoor | Indoor |
| Sensor Coverage | 600 sq ft | Wattage | 700 W |
| Mounting Type | Wall Box | On Function | Selectable Auto/Manual |
| Operating Humidity | 0-95% RH (Non-Condensing) | Sensing Range | Major Motion 35 ft, Minor Motion 20 ft |
| Wire Connection Type | Screw Terminals | Voltage | 120 VAC |
| Connection Type | Internal Pressure Plates | Load Type | CFL, Halogen, Incandescent, LED |
| Environmental Conditions | Residential Indoor Use Only | | |