



Control your lights, and even adjust the light level, with just a soft tap of a finger thanks to inventive micro-movement technology. Use this dimmer switch on its own to control an incandescent or halogen light or fixture from a single location, or pair with another remote dimmer switch for 3-way control a single light source from two locations.

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with dimmable incandescent/halogen bulbs or fixtures. Perfect for adding precise light level control -- all it takes is a soft tap to turn on/off or adjust brightness.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

|                        |                |                         |                           |
|------------------------|----------------|-------------------------|---------------------------|
| Product Line           | Pass & Seymour | Replaced by Part Number | ADTP703TUM4               |
| Color                  | Magnesium      | UPC Number              | 785007023275              |
| Country Of Origin      | China          | Features                | Indicator Lights          |
| Switch Type            | sofTap         | Number of Switches      | 1                         |
| Device Front Face Size | Full-Size      | Device Backbody Size    | Plus-Size                 |
| Standard               | cULus          | Warranty Type           | Limited Lifetime Warranty |
| Type                   | Dimmer         |                         |                           |

### Dimensions

---

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 2.51 in | Product Depth US | 1.79 in |
|------------------|---------|------------------|---------|

---

|                   |        |
|-------------------|--------|
| Product Height US | 4.2 in |
|-------------------|--------|

---

#### Technical Information

---

|                   |   |            |                 |
|-------------------|---|------------|-----------------|
| Electrical Rating | 120V 700W (Halogen), 120V 700W (Incandescent) | Connection | Screw Terminals |
|-------------------|---|------------|-----------------|

---

|                 |   |                    |                       |
|-----------------|---|--------------------|-----------------------|
| Number of Gangs | 1 | Bulb Compatibility | Halogen, Incandescent |
|-----------------|---|--------------------|-----------------------|

---

|                 |                    |         |        |
|-----------------|--------------------|---------|--------|
| Number of Poles | 3-Way, Single Pole | Wattage | 1100 W |
|-----------------|--------------------|---------|--------|

---

|               |     |
|---------------|-----|
| Mounting Type | Box |
|---------------|-----|

---