



Working in conjunction with an adore Hub and a Whisper Wi-Fi Ready Master Dimmer for 3-way control. Use the dimmer to turn lights on/off, or adjust brightness, all with just a fluid, whisper-soft motion. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Dimmer, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adore Wi-Fi Lighting Control System, this device requires the adore Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428431374	Country Of Origin	China
Features	Indicator Lights, Smart Lighting	Switch Type	Whisper
Number of Switches	1	Works With	Amazon Alexa, Control4, Elan, Google Assistant, Radio Frequency, RTI, URC

Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Residential	Standard	UL, FCC, cULus, RoHS
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	4.2 in	Product Depth US	1.79 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes	FCC Compliant	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)	Number of Gangs	1
Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	3-Way, Multi-Location, Single Pole
Requires Neutral Wire	Yes	Mounting Type	Box
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80% (relative humidity, non-condensing)