




adorne Collection
adorne® Plus Size Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles, Magnesium
Part No. AGFTR2153M4



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. *GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.

Replaces any standard outlet with ease, in as little as 10 minutes.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007052619
Country Of Origin	China	Number of Receptacles	2
Device Front Face Size	Plus-Size	Device Backbody Size	Plus-Size
Outlet Type	GFCI, Self-Test, Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty

Type	Outlet
------	--------

Dimensions

Product Width US	1.82 in	Product Depth US	1.76 in
------------------	---------	------------------	---------

Product Height US	3.0 in
-------------------	--------

Technical Information

Is Tamper-Resistant	Yes	Phase	Single
---------------------	-----	-------	--------

Connection	Side & Back Wire	Number of Gangs	1
------------	------------------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

Mounting Type	Box	Connection Type	Internal Pressure Plates
---------------	-----	-----------------	--------------------------

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---
