



A modern upgrade for style and safety, this tamper-resistant designer outlet from the adorne Collection installs easily for the basic power every home needs, while elevating your space. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Replaces any standard outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007022704
Country Of Origin	China	Number of Receptacles	2
Device Front Face Size	Full-Size	Device Backbody Size	Full-Size
Outlet Type	Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	1.77 in	Product Depth US	1.73 in
------------------	---------	------------------	---------

Product Height US 2.12 in

Technical Information

Phase	Single	Connection	Side and Back Wire
-------	--------	------------	--------------------

Number of Wires	3	Number of Gangs	1
-----------------	---	-----------------	---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Mounting Type	Box	Connection Type	Internal Pressure Plates
---------------	-----	-----------------	--------------------------

Environmental Conditions	95% (relative humidity, non-condensing)		
--------------------------	---	--	--
