




adorne Collection  
**3.1A adorne® USB Outlet, Type A Module, Graphite**  
Part No. ARUSB2AA6G4



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the adorne® Collection. Delivering a leading 6 amps of power to its two USB connections for faster in-wall charging, without an adapter. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Replaces a traditional outlet easily, in as little as 10 minutes.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Graphite
UPC Number	785007262360	Country Of Origin	China
Number of Receptacles	0	Features	USB-A Charging
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Outlet Type	Tamper-Resistant, USB-Charging	Application Sector	Commercial, Residential
Standard	yes	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

### Dimensions

---

Product Width US	1.77 in	Product Depth US	1.7 in
------------------	---------	------------------	--------

---

Product Height US	2.65 in
-------------------	---------

---

### Technical Information

---

USB Amperage	6 A	Connection	USB Type A/A
--------------	-----	------------	--------------

---

Number of USBs	2	Number of Gangs	1
----------------	---	-----------------	---

---

USB Power Output	15 W	Number of Poles	Double Pole
------------------	------	-----------------	-------------

---

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

---

Connection Type	Internal Pressure Plates	Environmental Conditions	95% [relative humidity, non-condensing]
-----------------	--------------------------	--------------------------	---

---