



adorne Collection  
adorne® USB Outlet, Type A, Half-Size, Magnesium  
Part No. ARUSBM4



Shown with one Half-Size USB Outlet

Get a full battery for your phones, tablets and more with the convenience of built-in charging. Features one USB Type-A connection. Pair with another half or standard-sized device to fill an adorne One-Gang or One-Gang+ Wall Plate. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate(not included). Available in a range of contemporary colors and stunning finishes.

Pairs with any other half-sized device to fit an adorne 1-Gang Wall Plate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Provides convenient built-in charging, without sacrificing a plug requiring a bulky adapter.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007022865
Country Of Origin	China	Features	USB-A Charging
Device Front Face Size	Half-Size	Device Backbody Size	Half-Size
Outlet Type	USB-Charging	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty

### Dimensions

---

Product Width US	1.81 in	Product Depth US	0.89 in
------------------	---------	------------------	---------

---

Product Height US	1.77 in
-------------------	---------

---

### Technical Information

---

USB Amperage	2.1 A	Phase	Single
--------------	-------	-------	--------

---

Connection	Side and Back Wire	Number of USBs	1
------------	--------------------	----------------	---

---

Number of Gangs	1	USB Power Output	11 W
-----------------	---	------------------	------

---

Amperage	15 A	Indoor/Outdoor	Indoor
----------	------	----------------	--------

---

Wattage	11 W	Mounting Type	Box
---------	------	---------------	-----

---

Connection Type	Internal Pressure Plates	Environmental Conditions	95% (relative humidity, non-condensing)
-----------------	--------------------------	--------------------------	---

---