



A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes one adapter to accept Legrand AVIP or Extron Electronics MAAP mini architectural adapter plates, Wiremold Open System adapters, and Ortronics TracJack and Series II mounting adapters. Modular Jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. AV3 Series Poke-Thru Devices require a 4" (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground	Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS)
Aluminum and brass flanges standard with black cover	Aluminum flange also available with an aluminum colored nonmetallic cover (AA)
Brass flange also available with brass colored nonmetallic cover (AB)	Modular Jacks sold separately
Modular Jacks sold separately	NOTE: Assembled with scrub water gasket
For use on tile or carpet floors	AV3 Series Poke-Thru Devices require a 4" (102mm) diameter hole
Not designed to work with bare concrete or terrazzo	For use on tile or carpet floors

Specifications

General Info

Product Line	Wiremold	UPC Number	786564015611
Country Of Origin	Mexico	Construction	Assembled
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Width US	8.25 in	Product Weight US	6.619 lb
------------------	---------	-------------------	----------

Product Height US	17.0 in	Core Hole Size	4 in
-------------------	---------	----------------	------

Knockout Size	1-1/4 in, 3/4 in
---------------	------------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Carpet, Tile, Wood	Service Capacity	Dual
------------	--------------------	------------------	------

Fire Rating	2 hr	Cable Entry	3/4 in Conduit Stem
-------------	------	-------------	---------------------

Number of Outlets	2
-------------------	---
