




adorne Collection  
adorne® Brushed Satin Brass 1-Gang+ Screwless Wall Plate  
Part No. AWC1G3BSB4



Classic brass goes modern in a milder metallic that transforms spaces with understated elegance. A 1-Gang Wall Plate, it is perfectly sized to fit a standard-sized adorne device, or any combination of two half-sized adorne designer switches or outlets.

## Features & Benefits

- Includes one Wall Plate and one Steel Frame for mounting the wall plate. A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.
- Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease. Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.
- Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

## Specifications

### General Info

|                        |                         |                 |                           |
|------------------------|-------------------------|-----------------|---------------------------|
| Product Line           | Pass & Seymour          | Color           | Brushed Satin Brass       |
| Finish                 | Satin                   | UPC Number      | 785007261561              |
| Country Of Origin      | Mexico                  | Wall Plate Size | Plus                      |
| Device Front Face Size | Plus-Size               | Wall Plate Type | Dimmer/Switch, Outlet     |
| Application Sector     | Commercial, Residential | Warranty Type   | Limited Lifetime Warranty |
| Type                   | Wall Plate              |                 |                           |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 3.45 in | Product Depth US | 0.35 in |
|------------------|---------|------------------|---------|

---

Product Height US      5.13 in

---

**Technical Information**

---

Thickness                      0.35 in                      Number of Gangs                      1

---

Indoor/Outdoor                      Indoor                      Mounting Type                      Screwless

---

Orientation                      Vertical

---