




adorne Collection  
adorne® Satin Black 4-Gang Screwless Wall Plate  
Part No. AWC4GSBL4



A dark base softened to a gentle finish, bringing something extraordinary into a room's décor. A 3-Gang Wall Plate, it is perfectly sized to fit any combination of up to three standard-sized adorne devices, or up to six half-sized adorne designer switches and outlets.

## Features & Benefits

- Includes one Wall Plate and one Steel Frame for mounting the wall plate.
- Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.
- Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.
- A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.
- Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

## Specifications

### General Info

|                    |                         |                 |                           |
|--------------------|-------------------------|-----------------|---------------------------|
| Product Line       | Pass & Seymour          | Color           | Satin Black               |
| Finish             | Satin                   | UPC Number      | 785007261752              |
| Country Of Origin  | Mexico                  | Wall Plate Type | Dimmer/Switch, Outlet     |
| Application Sector | Commercial, Residential | Warranty Type   | Limited Lifetime Warranty |
| Type               | Wall Plate              |                 |                           |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 8.88 in | Product Depth US | 0.35 in |
| Product Height US | 5.13 in |                  |         |

---

## Technical Information

---

|           |         |                 |   |
|-----------|---------|-----------------|---|
| Thickness | 0.35 in | Number of Gangs | 4 |
|-----------|---------|-----------------|---|

---

|                |        |               |           |
|----------------|--------|---------------|-----------|
| Indoor/Outdoor | Indoor | Mounting Type | Screwless |
|----------------|--------|---------------|-----------|

---

|             |          |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|

---