



**Wiremold**  
**GFCI PLUGMOLD 5FT BLACK 9 OUTLETS AND SELF TEST GFCI MODULE**  
Part No. BK20GB506TRGF16



Plugmold® Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil® harnesses of prewired receptacles, and cord-ended units. Plugmold® Multioutlet Systems are available in black or ivory ScuffCoat™ finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

## Features & Benefits

Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776188028
Country Of Origin	United States	Number of Receptacles	1
Application Sector	Residential	Standard	cULus Listed Base & Blank Cover: File e4376 Guide RJBT, Multi-Outlet Assemblies: File E15191 Guide PVGT, Fittings: File E41751 Guide RJPR, Base & Blank Cover: Meets Article 386 of NEC, Plugmold Strips: Meets Article 380 of NEC
Type	Plugmold		

### Dimensions

Product Width US	1.3 in	Product Weight US	3.17 lb
Product Depth US	0.75 in	Product Length US	1.3 in

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

---

#### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

#### Technical Information

---

Amperage	20 A	Enclosure Type	Steel
----------	------	----------------	-------

---

Voltage	125.0 V
---------	---------

---