

Wide range, Straight male, Dust tight grips. 1-inch NPT, 0.700-0.970-inch



Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

700 lbs breaking strength rating (in US lbs)

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007996180
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Dust Tight		

Dimensions

Product Width US	1.0 in	Product Length US	1.0 in
------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range 0.7 in

Minimum Cable Range 1 in

Capacity

Various Cable Diameter Ranges

Mounting

Consult the Factory
for Mounting
Recommendations

Load

Strain Relief Grips are designed to prevent
tension from being transferred to junctions
and terminals on electrical cord
