



Slide Dimmer, Single Pole 700W 120V, Ivory

Features & Benefits

Field configurable wall plate system.

Adjustable top end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	WSCL450TC
Color	Ivory	UPC Number	785007301717
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 95219

cULus Listed

Yes

Technical Information

Operating Cycles 100

Number of Poles

Single Pole

Wattage 700 W

Environmental Conditions

Non-Condensing Humidity:
Less than 95%
