



Pass and Seymour
Discontinued - Titan™ Series Fluorescent 2-Wire Dimmer, Black
Part No. CDFB163PBK



Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

| | |
|--|---|
| For use with 2 wire 120V and 277V fluorescent dimming ballasts | Field configurable wall plate system |
| Labeling system | Adjustable low end output voltage |
| Shipped with protective film | Rugged construction |
| Superior ratings with a minimum of derating when ganged | Simple to plan the rough-in |
| Available in single pole slide-to-OFF and single pole/3-way preset models | Attractive European styling. Eye-catching packaging |
| Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system | Blank center plate included |

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007303193 | Country Of Origin | China |
| Application Sector | Commercial | Standard | cULus, California Title 24 Compliant |
| Type | Dimmer | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

Operating Cycles

100

Amperage

16 A

Environmental Conditions

Non-Condensing Humidity: Less
than 95%
