Pass and Seymour

Discontinued - Titan Series Magnetic Low-Voltage Dimmer, Gray

Part No. CDLV1100GRY



Slide Dimmer, Low-Voltage, Single Pole-1100VA, Gray

Features & Benefits

- Field configurable wall plate system.
- Adjustable low end output voltage.
- Rugged construction.
- Simple to plan the rough-in.
- Attractive European styling.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.
- For covering patents, see www.legrand.us/patents.
- Labeling system.
- Shipped with protective film.
- Superior ratings with a minimum of de-rating when ganged.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Eye-catching packaging.
- Blank center plate included.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	1100 A	Number of Poles	Single Pole
Voltage	120 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		