



Ortronics

DO NOT USE Cisco® CFP-40G-LR4 Compatible 40GBase-LR4 CFP Transceiver Module with Digital Optical Monitoring
Part No. CFP-40G-LR4-LEG

This Cisco® CFP-40G-LR4 compatible CFP transceiver provides 40GBase-LR4 throughput up to 10km over single-mode fiber (SMF) at a wavelength of 1310nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent Cisco® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

LC ports designed for use with Single-Mode Fiber

Supports up to 10 kilometers of cabling

Supports Digital Optical Monitoring (DOM)

CFP transceiver module

1310nm wavelength signaling

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120668831	Country Of Origin	United States
Application Sector	Commercial/Industrial	Type	Transceiver

Trade Programs

TAA Compliant Yes

Additional Information

RoHS Compliant Yes Product Has Potential to Contribute to LEED Yes