



Pass and Seymour  
**1200 Series Cable Reel with 20A Quad Receptacle Box 20 Amp, 12 AWG, 25 ft For Lift/Drag Applications**  
Part No. CR12L123N25R20



Industrial-grade 1200 Series Cable Reels are precision machines, built with a minimum of components to provide years of reliable service with little or no maintenance. Made of all steel construction in the USA, these cable reels are ideal for assembly and fabrication work areas, conveyors, utility trucks, automotive and truck work bays, and much more.

## Features & Benefits

Made in USA All steel construction with fiberglass/nylon drum, yellow powder coat finish

UL/CSA Listed

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	CR12L123N50F20
Color	Yellow	UPC Number	785007205817
Country Of Origin	United States	Features	Lift/Drag, Retractable
Application Sector	Commercial, Data Center, Education, Industrial	Warranty Type	1-Year
Type	Cable Reel		

### Technical Information

Wire Gauge	12 AWG	Cord Length	25 ft
Amperage	20 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Quad Receptacle Box
Operating Temperature	22°-194°F	Voltage	125.0 V