



Pass and Seymour
1200 Series Cable Reel with 20A Quad Receptacle Box 20 Amp, 12 AWG, 50 ft For Lift/Drag Applications
Part No. CR12L123N50R20



Industrial-grade 1200 Series Cable Reels are precision machines, built with a minimum of components to provide years of reliable service with little or no maintenance. Made of all steel construction in the USA, these cable reels are ideal for assembly and fabrication work areas, conveyors, utility trucks, automotive and truck work bays, and much more.

Features & Benefits

Made in USA All steel construction with fiberglass/nylon drum, yellow powder coat finish

UL/CSA Listed

Specifications

General Info

| | | | |
|---------------|------------------------|--------------------|--|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007205800 | Country Of Origin | United States |
| Features | Lift/Drag, Retractable | Application Sector | Commercial, Data Center, Education, Industrial |
| Warranty Type | 1-Year | Type | Cable Reel |

Technical Information

| | | | |
|-----------------------|-----------|----------------------|---------------------|
| Wire Gauge | 12 AWG | Cord Length | 50 ft |
| Amperage | 20 A | Number of Conductors | 3 |
| Indoor/Outdoor | Indoor | Mobile End | Quad Receptacle Box |
| Operating Temperature | 22°-194°F | Voltage | 125.0 V |