



Pass and Seymour  
Discontinued - 1400 Series Cable Reel with Flying Lead 10A, 16 AWG, 70 ft For Lift/Drag Applications  
Part No. CR14L163N70F10B



The 1400 Series Industrial Cable Reels are the professionals choice for demanding industrial applications where reliability and versatility are paramount. Made in the USA with a minimum of components, these reels are ideal for assembly and fabrication work areas, Class A/C overhead cranes and hoists, schools and theaters, and much more.

## Features & Benefits

Made in USA	Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
NEMA 4 rated enclosure	UL and CSA Listed

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007206562	Country Of Origin	United States
Features	Lift/Drag, Retractable	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	1-Year	Type	Cable Reel

### Technical Information

Wire Gauge	16 AWG	Cord Length	70 ft
Amperage	10 A	Number of Conductors	3
Indoor/Outdoor	Both	Mobile End	Flying Lead
Operating Temperature	22°-194°F	Voltage	600.0 V