



Pass and Seymour
1400 Series Cable Reel with Flying Lead 20A, 10 AWG, 40 ft For Stretch Applications
Part No. CR14S104N40F20



The 1400 Series Industrial Cable Reels are the professionals choice for demanding industrial applications where reliability and versatility are paramount. Made in the USA with a minimum of components, these reels are ideal for assembly and fabrication work areas, Class A/C overhead cranes and hoists, schools and theaters, and much more.

Features & Benefits

Made in USA	Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
NEMA 4 rated enclosure	UL and CSA Listed

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007206098	Country Of Origin	United States
Features	Retractable, Stretch	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	1-Year	Type	Cable Reel

Technical Information

Cord Length	40 ft	Amperage	20 A
Number of Conductors	4	Indoor/Outdoor	Both
Mobile End	Flying Lead	Operating Temperature	22°-194°F
Voltage	600.0 V		