

Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.



## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                    |                    |              |
|-------------------|--------------------|--------------------|--------------|
| Product Line      | Pass & Seymour     | Color              | White        |
| Finish            | Matte              | UPC Number         | 785007126471 |
| Country Of Origin | Mexico             | Application Sector | Commercial   |
| Standard          | UL 498/20, FEDSPEC |                    |              |

### Dimensions

---

|                  |         |                  |          |
|------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |
|------------------|---------|------------------|----------|

---

|                   |          |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Technical Information

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Single Pole |
|----------|------|-----------------|-------------|

---

|           |               |
|-----------|---------------|
| Wire Size | #14 - #10 AWG |
|-----------|---------------|

---