



Ortronics

Discontinued - Cisco CWDM-SFP-1550-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1550nm, 40km, LC Duplex, DDM, I-Temp)  
Part No. CWDM-SFP-1550-40-L



Cisco CWDM-SFP-1550-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1550nm, 40km, LC Duplex, DDM, I-Temp)

## Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.
- Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

## Specifications

### General Info

|                   |             |               |              |
|-------------------|-------------|---------------|--------------|
| Product Line      | Ortronics   | UPC Number    | 662875060413 |
| Country Of Origin | China       | Warranty Type | Lifetime     |
| Type              | Transceiver |               |              |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 13.9 mm | Product Depth US | 58.4 mm |
| Product Height US | 8.5 mm  |                  |         |

### Technical Information

|                           |             |                           |       |
|---------------------------|-------------|---------------------------|-------|
| Fiber Optic Cable Type    | Single-Mode | Max Distance Support      | 40 km |
| Operating Temperature Min | -40 °C      | Operating Temperature Max | 85 °C |
| Connector Type            | LC Duplex   | Form Factor               | SFP   |