



Wattstopper Seven Button LV Decorator Switch, Contact Closure, White Part No. DCC7-W



The Decorator Seven-button Low Voltage Momentary Switch (DCC7) features a raise/lower paddle and five buttons to control any device that requires multiple contact closures. It is available in four colors, and is compatible with other Decorator style products, including the DCC2 Low Voltage Momentary Decorator Switch with LED.

Features & Benefits

Collection consolidated to white option

Long-life LED locator

Five buttons and two-position paddle provide seven contact closures

Compatible with Decorator styling

Available in four colors

Controls wide variety of common system protocols

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182922871
Country Of Origin	China	Switch Type	Push, Rocker
Number of Switches	6	Application Sector	Commercial
Standard	UL, RoHS	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.7 in	Product Weight US	0.2 lb
Product Volume US	14.3 cu in	Product Depth US	2.0 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Load Rating	50 mA @ 24 VDC/VAC
---------------------------	-------	-------------	--------------------

Has Battery	No	Operating Temperature Max	104 °F
-------------	----	---------------------------	--------

Number of Buttons	5	Input Voltage	12 VDC/VAC, 24 VDC/VAC
-------------------	---	---------------	------------------------

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

Operating Temperature	32°-104°F	Operating Humidity	0-80% RH (Non-Condensing)
-----------------------	-----------	--------------------	---------------------------

Wire Connection Type	Flying Leads	Engraving Type	Blank
----------------------	--------------	----------------	-------

Storage Temperature	23° - 176° F, -5° - 80° C
---------------------	---------------------------
