



Pass and Seymour
DR Series CFL/LED/Incandescent Single Pole/3-Way Rotary Dimmer, Preset, Brown
Part No. DRCL453P



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

Convenient Operation - Combines ON/OFF Decorator style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products Higher ratings

Single pole and 3-way operation

Screw-pressure-plate back wire terminals to save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Gloss	UPC Number	785007055412
Country Of Origin	China	Product Series	Decorator
Features	Lighted, Low-End Trim (Dim Range)	Switch Type	Rocker, Rotary, Single Pole 3-Way
Number of Switches	1	Application Sector	Residential
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
------------------	---------	------------------	---------

Product Height US 4.19 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
--------	-----	-------------	---

Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
-----------------------	---------------	------------------	-------

Number of Poles	Single Pole 3-Way	Requires Neutral Wire	No
-----------------	-------------------	-----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Screw Terminals	Voltage	120 VAC
----------------------	-----------------	---------	---------

Load Type	CFL, Halogen, Incandescent, LED
-----------	---------------------------------
