




Wiremold
Evolution™ Series Ten Gang Floor Box
Part No. EFB10S



The Evolution™ Series Ten Gang Floor Box has been designed to be installed in concrete, raised, and wood floor applications. The box has a fully finished interior to assist plugging and unplugging of devices. Designed to work with standard size multigang wall plates, or proprietary plates for a full ten gangs of capacity. It comes complete with all components needed for initial installation. The floor box is compatible with Walkerflex Modular Wiring System. Custom options are available upon request.

Features & Benefits

The Evolution™ Series Ten Gang Floor Box has been designed to be installed in concrete, raised, and wood floor applications. The box has a fully finished interior to assist plugging and unplugging of devices.

Designed to work with standard size multigang wall plates, or proprietary plates for a full ten gangs of capacity. It comes complete with all components needed for initial installation.

The floor box is compatible with Walkerflex Modular Wiring System. Custom options are available upon request.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776176452	Country Of Origin	United States
Construction	Assembled	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	12.75 in	Product Weight US	22.333 lb
Product Volume US	1233.95 cu in	Product Depth US	16.13 in
Product Height US	6.0 in	Cubic Capacity	27.3 in ³

Knockout Size	1-1/4 in, 2 in, 3/4 in
---------------	------------------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Concrete, Raised, Wood	Service Capacity	Triple
------------	------------------------	------------------	--------

Minimum Floor Depth	2 in	Box Capacity	10 Gangs
---------------------	------	--------------	----------

Cable Entry	knockout	Box Type	Recessed
-------------	----------	----------	----------

Number of Outlets	0	Depth Behind Device Plates	3.5 in
-------------------	---	----------------------------	--------
