




Wiremold  
**EFB6S-FC1122 Evolution Series 6-Gang Fire-Classified Floor Box**  
Part No. EFB6S-FC1122



6-Gang Fire Classified Floor Box Pre-assembled installation ready Floor Box has been designed to be installed in above grade concrete floors while maintaining the fire classification of the floor. This box is classified to be used in 1-, 1 1/2-, 2-, or 3-hour fire rated floors. Designed to accept standard size wall plates. Box comes complete with all components needed for initial installation.

## Features & Benefits

6-Gang Fire Classified Floor Box Pre-assembled installation ready Floor Box has been designed to be installed in above grade concrete floors while maintaining the fire classification of the floor.

This box is classified to be used in 1-, 1 1/2-, 2-, or 3-hour fire rated floors. Designed to accept standard size wall plates. Box comes complete with all components needed for initial installation.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776184129
Country Of Origin	United States	Construction	Assembled
Number of Knockouts	1	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

### Dimensions

Product Width US	17.25 in	Product Weight US	47.0 lb
Product Depth US	4.25 in	Product Length US	21.75 in
Cubic Capacity	32 in <sup>3</sup>	Knockout Size	2 in, 3/4 in

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Floor Type	Concrete, Raised, Wood	Service Capacity	Triple
------------	------------------------	------------------	--------

---

Minimum Floor Depth	2 in	Fire Rating	3 hr
---------------------	------	-------------	------

---

Box Capacity	6 Gangs	Cable Entry	CONDUIT
--------------	---------	-------------	---------

---

Box Type	Above-Grade, Fire Classified	Depth Behind Device Plates	3.88 in
----------	------------------------------	----------------------------	---------

---