



Wiremold
Evolution™ Series 4-Gang Hinged Wall Box
Part No. EHWB4-BK



Designed to fit into the 16in on center (406mm) opening between studs in a standard 2in x 4in (51mm x 102mm) wall. For both new work and old work applications. The box has 4-gang standard NEMA size openings and is designed to accommodate power, communications, and A/V devices. The box has been designed with a cable pass-through capability, allowing multiple service access points to be daisy chained together, eliminating the need for multiple conduit runs. Box includes temporary cover. Finished cover assembly (EHWBC4) sold separately.

Features & Benefits

Available in both 4- and 8-gang versions to provide maximum flexibility.

Cover opens a full 180° and can be painted to blend with room decor. Includes integrated handle, lock and key set for security, and flush egress door for cabling.

Accepts Legrand AVIP devices, plus A/V devices from leading manufacturers.

Accepts trade size service feeds from 3/4" up to 2". Knockout plates are removable and interchangeable, providing multiple options.

Both boxes (4- and 8-gang) fit are designed to fit in 16" opening between studs in standard 2" x 4" [51mm x 102mm] wall.

Finished interior eliminates industrial look for upscale installations, while increasing visibility, making it easier to locate.

Built-in tunnel & feed through capability allows service feeds to be fed through the box, reducing the number of feeds required to reduce installation time.

Designed to accept standard 1- to 4-gang device plates. No proprietary plates simplifies ordering and installation.

3 5/8" [92mm] of space behind device plates provides the extra depth needed for wiring larger A/V devices.

Can be installed in new work and old work installations. New hardware not necessary.

UL Listed to U.S. and Canadian safety standards.

Specifications

General Info

| | | | |
|--------------|--------------|--------------------|---|
| Product Line | Wiremold | Color | Black |
| UPC Number | 786564085621 | Country Of Origin | United States |
| Construction | Assembled | Application Sector | Commercial, Education, Healthcare, Hospitality |

| | | | |
|----------|---|------|----------|
| Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. | Type | Wall Box |
|----------|---|------|----------|

Dimensions

| | | | |
|------------------|--------------------|-------------------|------------------------|
| Product Width US | 7.98 in | Product Weight US | 6.49 lb |
| Product Depth US | 3.98 in | Product Length US | 10.98 in |
| Cubic Capacity | 43 in ³ | Knockout Size | 1-1/4 in, 2 in, 3/4 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------------|----------|----------------------------|---------|
| Service Capacity | Dual | Number of Gangs | 4 |
| Cable Entry | knockout | Depth Behind Device Plates | 3.63 in |
