



On-Q
14-inch Enclosure with Screw-On Cover
Part No. EN1400



This 14" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes

Features & Benefits

| | |
|---|---|
| 14-in Enclosure with Screw-On Cover | Drywall depth indicators |
| Flush and surface installation | Mounting tabs provide correct flush-mount position for standard installations |
| Patented mounting system offers versatile module mounting options | Cover included |
| Made in the USA | |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|--|
| Product Line | On-Q | Color | White |
| UPC Number | 804428023012 | Country Of Origin | United States |
| Application Sector | Residential | Standard | UL (UL985, UL1023, UL1863), cULus, CSA, RoHS |
| Type | Enclosure | | |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 14.25 in | Product Depth US | 3.6 in |
| Product Height US | 14.0 in | | |

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Additional Information

RoHS Compliant

Yes

Technical Information

Thickness

0.1 in

Cable Entry

(6) rear knockouts

Frame

Cold Rolled Steel
